

SONATEC

SONATEC INNOVATION

For the fast and accurate determination of the concentration of a liquid in a tank, a very specific ATEX compliant version of SONATEC is available. Installed on the tank top, the measuring head of this customized device can be immersed into the tank to a depth of 2 metres. The extremely rigid design has a proven track-record in various industries and applications. It can be adapted for vessels that are equipped with agitators and mixers.



Innovation. Dedication. Centec.

Germany
Centec GmbH
Wilhelm-Röntgen-Strasse 10
63477 Maintal
Tel.: +49 6181 18 78 0
Fax: +49 6181 18 78 50
info@centec.de

Czech Republic
Centec automatika s.r.o.
Pekařská 8/601
155 00 Praha 5
Tel.: +420 257 084 111
Fax: +420 235 518 701
prodej@centec.cz

USA
Centec LLC
P. O. Box 820
Germantown, WI 53022-0820
Tel.: +1 262 251 8209
Fax: +1 262 251 8376
info@centec-usa.com

UK distributor:
Protecnica Solutions Ltd
info@protecnica.co.uk
www.protecnica.co.uk

UK
Centec UK
Stalworths, The Street
Great Tey, Colchester, Essex, CO6 1JS
Tel.: +44 1206 21 19 21
Fax: +44 1206 21 19 16
info@centec-uk.com


Serbia
Centec Serbia
Bogdana Žerajića 34/III
11000 Beograd
Tel.: + 381 11 358 11 24
Fax: + 381 11 358 11 24
info@centec.rs

India
Centec RRR Systems & Sensors Pvt Ltd
RRR House, Plot 80, Sector 23
Turbhe Naka, Navi Mumbai - 400 705
Tel.: +91 22 2783 3655 & 2783 1348
Fax: +91 22 2783 4814
mail@centecrrr.com

Brazil
Centec América Latina Ltda
Largo de Sao Francisco de Paula nº 26
Centro Cep. 20051 070 Rio de Janeiro
Tel.: +55 21 2223 2066
Fax: +55 21 2223 0324
centeclatina@terra.com.br

Determination of Concentration by Sound Velocity

Centec Process Sensors



Automated process skids and high precision sensors from a single source. Centec.

SONATEC

The Principle

SONATEC continuously measures the velocity of sound through liquids. Designed for applications that require maximum sensitivity and high accuracy, this device is used in various industries all around the world. Breweries and beverage manufacturers determine extract or dissolved sugar contents in-line with SONATEC. Equipped with an integrated cleaning nozzle, SONATEC HW can be installed directly into brewery wort kettles and evaporators. In numerous pharmaceutical and chemical applications SONATEC is used to control the concentration of acids, caustics and other solutions – but also for monitoring the quality of raw materials and final products. The instrument measures the speed of a sound pulse between a transmitter and a receiver. The sound pulse is created by piezo-elements and moves perpendicular to the product flow. As a specific property of each liquid, the correlation between concentration and sound velocity can be described by a mathematical polynomial. With decades of experience and own laboratory facilities, we have a particular knowledge about polynomials for a huge number of products. Any temperature drifts of the measured signal are automatically compensated for by an internal Pt1000 sensor. SONATEC displays various units, e.g. vol.%, mass %, °Brix and °Plato.



SONATEC
Transmitter Version



SONATEC HW
Transmitter Version
for the Wort Kettle

- Available as Transmitter Version with Local Display and as a Sensor
- Highly Precise and Fast Determination of the Concentration
- Based on Sound Velocity Measurement
- Applicable for a Huge Number of Liquids in Various Industries
- Short Response Time and Excellent Long-Term Stability
- Hygienic Execution, Full CIP Capability and Maintenance Free
- Outstanding Price-Performance-Ratio

Technical Data	SONATEC	SONATEC HW
Measuring Range	400 - 3.000 m/s	400 - 3.000 m/s
Accuracy	± 0,05 m/s	± 0,05 m/s
Reproducibility	± 0,01 m/s	± 0,01 m/s
Response Time	≤ 1 s	≤ 1 s
Inlet Pressure	max. 16 bar	max. 16 bar
Temperature of Operation	- 25 - + 125 °C	- 25 - + 125 °C
Temperature Compensation	Pt1000	Pt1000
Material (Standard)	1.4404/AISI 316L	1.4404/AISI 316L
Material (Option)	1.4571/AISI 316 Ti; Hastelloy C276; Monel 400; Incoloy 825; Tantalum; others on request	on request
Connections	Varivent© DN65; diary pipe DIN11851 DN65; DIN; ANSI; others on request	DIN2633 DN100; others on request
Input Transmitter Version	6 x digital (24 VDC)	1 x digital (24 VDC)
Output Transmitter Version	3 x digital (24 VDC) & 2 x analog (4 - 20 mA)	3 x digital (24 VDC) & 2 x analog (4 - 20 mA)
Profibus DP Transmitter Version	option	option
Sensor (w/o local display)	standard	standard
Enclosure Rating	IP65	IP65
Explosion Protection Ex II 2G EEx d IIC T6	option	-
Power Supply	24 VDC	24 VDC

The Centec production is certified according to ISO 9001.